



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S61510CT00 1-1/2" SS316 Rigid Conduit, 10' W/Coupling

Cablofil

Catalog Number	S61510CT00
Manufacturer	Cablofil
Description	Rigid Conduit, 316 Stainless Steel Material; Bright Polished Finish; 10 FT; 1.61 Inch Inner Diameter; 1.9 Inch Outer Diameter; UI/Cul 6A, Csa C22.1 Approval; Ansi/Nfpa 70, Nec Applicable Standard; 2.63 LB Per FT Weight; 1-1/2 Inch Trade Size
Weight per unit	2.6 (lbs/each)
Product Category	Galvanized Heavy Wall Conduit

Features

Applicable Standard	ANSI/NFPA 70, NEC
End Style	Threaded
Material	316 Stainless Steel

Material, Color, and Finish

Finish	Bright Polished
--------	-----------------

Dimensions and Weight

Inner Diameter	1.61 Inch
Length	10 ft
Outer Diameter	1.9 Inch

Descriptions

Additional Information	Thread Size 11.5 TPI
Commodity Description	Galvanized Rigid Steel Conduit
Description	1-1/2" SS316 RIGID CONDUIT, 10' W/COUPLING
extra long description	316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 1.61 INCH INNER DIAMETER; 1.9 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 1-1/2 INCH TRADE SIZE; THREADED END STYLE; CALBRITE BRAND; THREAD SIZE 11.5 TPI; WEIGHT 2.63 LB PER FT
Long Description	RIGID CONDUIT, 316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 1.61 INCH INNER DIAMETER; 1.9 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 2.63 LB PER FT WEIGHT; 1-1/2 INCH TRADE SIZE
Product Type	Rigid Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	CALPIPE INDUSTRIES, INC.
GTIN	00847656000141
Manufacturers Part Number	S61510CT00
UPC	847656000141

Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
----------------------	-------------------------

Trade Size

Trade Size	1-1/2 INCH
------------	------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	10
Weight	2.63 Lb per Ft
Weight Per each	2.63

Uses, Certifications, and Standards

Approval	UL/CUL 6A, CSA C22.1
----------	----------------------