



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SB1408S 14-8AWG STL Crimp Sleeve

Nsi Industries

Catalog Number	SB1408S
Manufacturer	Nsi Industries
Description	The Easy-Twist SB1408S 50-Count Pack Of Steel Crimp Sleeve Wire Connectors Are Designed For Use On Wires In The 14-8 Awg Size Range. The Simple Brass-Plated Sleeve Design Forms Low-Resistance Connections In A Tight Space and Installs Using A Specialized Crimp Tool or Adjustable Pliers. Use Crimp Sleeves to Permanently Connect Wires In Grounding, Uninsulated or Small Motor Applications Where Vibration Resistance Is A Concern.
Weight per unit	0.5000 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Steel
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	14-8 AWG
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Steel
Finish	Steel

Dimensions and Weight

Size	L=.610 - W=.364 - ID=.263
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	14-8AWG STL CRIMP SLEEVE
extra long description	NSI SB1408S Crimp Sleeve 14-8 Steel
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. The steel crimp sleeve wire connector provides a quick, economic and vibration-resistant way to form permanent connections in most applications. Simply twist your wires to form a connection, then slide the sleeve—sometimes called a ground cap—down to the twist and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these brass-plated steel cri
Long Description	The Easy-Twist SB1408S 50-Count Pack of Steel Crimp Sleeve Wire Connectors are designed for use on wires in the 14-8 AWG size range. The simple brass-plated sleeve design forms low-resistance connections in a tight space and installs using a specialized crimp tool or adjustable pliers. Use crimp sleeves to permanently connect wires in grounding, uninsulated or small motor applications where vibration resistance is a concern.
Product Type	Crimp Sleeve 14-8 Steel, PK Of 50
Special Features	Steel Crimp Sleeves - 100 Pcs Blister

Manufacturer Information

Brand	Easy-Twist
GTIN	00662381402455
Manufacturers Part Number	SB1408S
UPC	662381402455

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Crimp Sleeve Wire Connectors

Packaging

Carton	1
Weight Per package	0.5

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C