

Eaton S811 R13P3S

Catalog Number: S811+R13P3S

Eaton S811+ soft starter, Soft Starter ,110 mm, 135 A, Pimp control with OPT Inside delta



Photo is representative

General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+R13P3S
UPC	Product Length/Depth
786685558967	13 in
Product Height	Product Width
10 in	9.5 in
Product Weight	Certifications
12.5 lb	Contact Manufacturer

Amperage Rating

42-135A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

Type

Premium

Frame size

R

Rating

30 kW at 230 V, 55 kW at 380-400 V, 59 kW at 440 V

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 2—Commercial Distribution

Product Datasheet - S811+R13P3S

Drawings

Type S811+ Soft Starter - N-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+N... and S811+R

Multimedia

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+R13P3S

Eaton S811 R13P3S

Catalog Number: S811+R13P3S

Eaton S811+ soft starter, Soft Starter ,110 mm, 135 A, Pimp control with OPT Inside delta



Photo is representative

General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+R13P3S
UPC	Product Length/Depth
786685558967	13 in
Product Height	Product Width
10 in	9.5 in
Product Weight	Certifications
12.5 lb	Contact Manufacturer

Amperage Rating

42-135A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

Type

Premium

Frame size

R

Rating

30 kW at 230 V, 55 kW at 380-400 V, 59 kW at 440 V

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 2—Commercial Distribution

Product Datasheet - S811+R13P3S

Drawings

Type S811+ Soft Starter - N-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+N... and S811+R

Multimedia

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+R13P3S