



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



SB475Z Tam 1G WP BRNZ Outlet BX

Hubbell--Raco

| | |
|------------------|---|
| Catalog Number | SB475Z |
| Manufacturer | Hubbell--Raco |
| Description | 1-Gang 4-Hole 3/4 In. Outlet Box - Bronze |
| Weight per unit | 0.6690 (lbs/each) |
| Product Category | Outlet Boxes, Etc. - Steel |

Features

| | |
|------------------|----------------|
| Knockouts | 3/4 IN Holes;4 |
| Material | Metal |
| number of outlet | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Bonze |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 1-Gang |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Construction | Die Cast |
| Description | TAM 1G WP BRNZ OUTLET BX |
| extra long description | RACO SB475Z 1G WP BOX (4) 3/4 IN. O |
| Long Description | 1-Gang 4-Hole 3/4 in. Outlet Box - Bronze |
| Product Type | 1G WP Box (4) 3/4 In. Outlets - Bronze |
| Special Features | TAYMAC Weatherproof outlet boxes are made of superior commercial quality die cast metal construction and are finished with a premium powdercoat. NEMA 3R compliant; 1 gang; 4 - 3/4" holes ; includes closure plugs, grounding screw, and mounting hardware; bronze. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Taymac |
| GTIN | 00092326114486 |
| Manufacturers Part Number | SB475Z |
| UPC | 092326114486 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | WEATHERPROOF BOXES & COVERS |
| Type | 1-Gang Bronze Four Hole Outlet Box - Four 3/4 IN Holes |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.669 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

| | |
|-------------|------------|
| Application | Electrical |
| standard | UL |