



S9193

13.5W/LED/7FLUSH/3K/DD

13.5 watt; 7" Flush Mount LED Fixture; 3000K; Deep Dish; 120 volts

Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- U.L. Approved - Damp location
- Dimmable

Compatible Dimmers

- Lutron® CL Family (96-101)
- Leviton® IPLO6 Universal
- Cooper® TAL06P-C1



S9193

Item Number	UPC	Watts	Fixture Type	Base	Lamp Code	Voltage	MOL In Inches
S9193	045923091933	13.5	Flush Mount	Direct Wired	13.5W/LED/7FLUSH/3K/DD	120	1 13/16"

MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent	Pack
7.00"	820	40000	3000	Warm White	80+	75W	12

Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Box	108	ENERGY STAR	Yes	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9193

13.5W/LED/7FLUSH/3K/DD

13.5 watt; 7" Flush Mount LED Fixture; 3000K; Deep Dish; 120 volts

Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- U.L. Approved - Damp location
- Dimmable

Compatible Dimmers

- Lutron® CL Family (96-101)
- Leviton® IPLO6 Universal
- Cooper® TAL06P-C1



S9193

Item Number	UPC	Watts	Fixture Type	Base	Lamp Code	Voltage	MOL In Inches
S9193	045923091933	13.5	Flush Mount	Direct Wired	13.5W/LED/7FLUSH/3K/DD	120	1 13/16"

MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent	Pack
7.00"	820	40000	3000	Warm White	80+	75W	12

Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Box	108	ENERGY STAR	Yes	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

