



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC55BX 10A Alligator Clip

Selecta Products

Catalog Number	SC55BX
Manufacturer	Selecta Products
Description	General Purpose Clip, General Purpose Test Type; Zinc Plated Finish; 2 Inch; 10 Ampere Max. Current Rating; Steel Contact Material; 7/16 Inch Jaw Opening; 1 Lead(S); Wire Attachment Crimp/Screw; SC Model
Weight per unit	N/A
Product Category	Testers & Accessories

### Features

Jaw Opening	7/16 INCH
Maximum Current Rating	10 Ampere
Number of Leads	1 PH

### Material, Color, and Finish

Contact Material	STEEL
Finish	Zinc Plated

### Dimensions and Weight

Length	2 INCH
--------	--------

### Descriptions

Additional Information	Wire Attachment Crimp/Screw
Commodity Description	Testers & Meters - Testers & Accessories
Description	10A ALLIGATOR CLIP
Long Description	GENERAL PURPOSE CLIP, GENERAL PURPOSE TEST TYPE; ZINC PLATED FINISH; 2 INCH; 10 AMPERE MAX. CURRENT RATING; STEEL CONTACT MATERIAL; 7/16 INCH JAW OPENING; 1 LEAD(S); WIRE ATTACHMENT CRIMP/SCREW; SC MODEL
Product Type	General Purpose Clip

### Manufacturer Information

Brand	SELECTA PRODUCTS, INC.
GTIN	00661191250553
Manufacturers Part Number	SC-55-BX
Model	SC
UPC	661191250553

### Taxonomies, Classifications, and Categories

Category Description	SIGNALING EQUIPMENT
Type	TEST



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685









## Packaging

Carton	1
Package	10
Weight Per each	0

## Uses, Certifications, and Standards

Application	GENERAL PURPOSE TEST
-------------	----------------------

**Battery/Crocodile/General Purpose Test/Mini-Gator/Welding**



Style	Amp Rating	Material/Plating	Clip Jaws Open	Jaw Length	Wire Attachment	Use w/ Insulator #	Part Number*	Fig. No.
Battery	40	Steel/Zinc	3/4"	21/32"	Crimp/Screw	26	SC-25	1
Battery	50	Steel/Zinc	1-1/16"	25/32"	Crimp/Screw	23	SC-21A	2
Battery	50	Steel/Copper	1-1/8"	1"	Crimp/Solder	Insulated	SC-46A <sup>1</sup>	3
Battery	75	Copper	3/4"	21/32"	Crimp/Screw	26	SC-25C	1
Battery	75	Copper	1-1/8"	1"	Crimp/Solder	Insulated	SC-46C <sup>1</sup>	3
Battery	100	Steel/Zinc	1-5/8"	1"	Lug	13	SC-11A	4
Battery	100	Copper	1-1/16"	25/32"	Lug	23	SC-21C	2
Battery	200	Copper	1-5/8"	1"	Lug	13	SC-11C	4
Crocodile	5	Steel/Zinc	5/16"	15/16"	Crimp/Screw	87	SC-85	5
Crocodile	10	Copper	5/16"	15/16"	Crimp/Screw	87	SC-85C	5
General Purpose Test	10	Steel/Zinc	5/16"	1/4"	Crimp/Screw	47	SC-45	6
General Purpose Test	10	Steel/Zinc	7/16"	3/8"	Crimp/Screw	49	SC-55	7
General Purpose Test	10	Steel/Zinc	1/2"	3/8"	Crimp/Screw	49	SC-48B	8
General Purpose Test	20	Steel/Zinc	5/8"	17/32"	Crimp/Screw	29	SC-27 <sup>2</sup>	6
General Purpose Test	20	Copper	1/2"	3/8"	Crimp/Screw	49	SC-48C	8
General Purpose Test	40	Copper	5/8"	17/32"	Crimp/Screw	29	SC-27C <sup>2</sup>	6
Mini-Gator	5	Steel/Nickel	3/16"	7/16"	Crimp/Solder	32	SC-30	9
Mini-Gator	5	Copper	3/16"	7/16"	Crimp/Solder	32	SC-30C	9
Welding	300	Copper	1-13/16"	1-1/4"	Lug	35	SC-33C	10

\* Contact Sales Department for different types of packaging available.

<sup>1</sup> Handles are insulated.

<sup>2</sup> Length 2-7/16"