

Specifications

Eaton SF500PH10X10



Photo is representative

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

General specifications

PRODUCT NAME	Eaton rotary disconnect shaft extension
CATALOG NUMBER	SF500PH10X10
UPC	786685408538
PRODUCT LENGTH/DEPTH	19.7 in
PRODUCT HEIGHT	0.39 in
PRODUCT WIDTH	0.39 in
PRODUCT WEIGHT	0.85 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Physical Attributes

SERIES	R9
TYPE	Shaft extension

Miscellaneous

PRODUCT CATEGORY	Shaft extensions for external handles
SIZE	500 mm (19.7 in)
SPECIAL FEATURES	Shaft for PH2 handle, I-J-,K-,L-,M-frame
USED WITH	Handle type: PH2, PH3

Performance Ratings

AMPERAGE RATING	100-400A
------------------------	----------

Resources

CATALOGS	Motor Control and Protection, Rotary Disconnects, Volume 5, Tab 8
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SF500PH10X10
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications

Eaton SF500PH10X10



Photo is representative

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

General specifications

PRODUCT NAME	Eaton rotary disconnect shaft extension
CATALOG NUMBER	SF500PH10X10
UPC	786685408538
PRODUCT LENGTH/DEPTH	19.7 in
PRODUCT HEIGHT	0.39 in
PRODUCT WIDTH	0.39 in
PRODUCT WEIGHT	0.85 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Physical Attributes

SERIES	R9
TYPE	Shaft extension

Miscellaneous

PRODUCT CATEGORY	Shaft extensions for external handles
SIZE	500 mm (19.7 in)
SPECIAL FEATURES	Shaft for PH2 handle, I-J-,K-,L-,M-frame
USED WITH	Handle type: PH2, PH3

Performance Ratings

AMPERAGE RATING	100-400A
------------------------	----------

Resources

CATALOGS	Motor Control and Protection, Rotary Disconnects, Volume 5, Tab 8
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SF500PH10X10
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.