



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SGB390CL 4" Diecast Mighty-Right Split Ground Bushing *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | SGB390CL |
| Manufacturer | Bridgeport Fittings |
| Description | Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 4 Inch, 14-1/0 Lug |
| Weight per unit | 0.5620 (lbs/each) |
| Product Category | Boxes & Covers |

Features

| | |
|----------|------------|
| Material | Zinc Alloy |
| media | Yes |

Material, Color, and Finish

| | |
|--------|---------------------------|
| Color | Grey with Black Insulator |
| Finish | Ball burnish |

Dimensions and Weight

| | |
|------|---|
| Size | 4 |
|------|---|

Descriptions

| | |
|------------------------|--|
| Description | 4" DIECAST MIGHTY-RIGHT SPLIT GROUND BUSHING |
| extra long description | BPT SGB-390CL 4" SPLT GND BSH W/LUG |
| Features | Split Bushings install after the wire pull. No more burning through bushings or fighting with pullers. Save time and effort too! |
| Long Description | Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 4 Inch, 14-1/0 Lug |
| Product Type | 4" SPLT GND BSH W/Lug #6-3/0 |
| Special Features | Grounding Lug Wire Capacity #6 - 250MCM |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747903907 |
| Manufacturers Part Number | SGB-390CL |
| UPC | 781747903907 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type | SPLIT |

Trade Size

| | |
|------------|---|
| Trade Size | 4 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 20

Weight Per each 0.562

Uses, Certifications, and Standards

Application Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated bushing is required. Rated 150 Degree C. cULus listed. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

standard cULus

Temperature Rating 150°C