



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **SJE00W143PCS 14/3 Sjeoow 300V Black Cord PCS** *Southwire Company*

Catalog Number	SJE00W143PCS
Manufacturer	Southwire Company
Description	Portable Cord, Stranded, 41/30 MM Core Strands, #14 Awg Conductor Size, Copper Conductor Material, Thermoplastic Jacket Material, Thermoplastic Insulation Material, 300 V, Black, Green and White, 3 Conductors, 250 FT Overall Length, 0.37 In Outside Diameter, 0.03 In Insulation Thickness, -50 °C Operating Temperature, +105 Operating Temperature, 0.086 LB
Weight per unit	0.0860 (lbs/ft)
Product Category	Sjeow-Sjeoow

### **Features**

Number of Conductors	3 in
Stranding	41/30 STRANDS

### **Material, Color, and Finish**

Color Code	BLACK, WHITE, GREEN
Jacket Color	BLACK

### **Dimensions and Weight**

Length	250 ft
Outer Diameter	0.365 INCH

### **Descriptions**

Additional Information	ROHS Compatible; Applicable Standard NEC 400, Federal Specification JC-580B; Current Rating 18 Ampere; Insulation Thickness 0.03 Inch
Commodity Description	SJEOW - SJEOW - 300V CORD & CABLE
Description	14/3 SJEOW 300V BLACK CORD PCS
extra long description	SJEOW TYPE; 250 FT; 0.365 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 62, CSA C22.2, MSHA APPROVAL; INDUSTRIAL CONTROL, MOTOR CONTROL, MINING, PORTABLE POWER DISTRIBUTION, PUSHBUTTON REMOTE CONTROL, ROBOTIC SYSTEM, STAGE EQUIPMENT, LIGHTING APPLICATION; 300 V VOLTAGE RATING; -50 TO 105 DEG C TEMPERATURE RATING; 3 CONDUCTOR(S); T-PRENE THERMOPLASTIC ELASTOMER INSULATION MATERIAL; 14 AWG CONDUCTOR SIZE; BLACK, WHITE, GREEN COLOR CODE; CHEMICAL/OIL/WATER RESISTANT SEOPRENE THERMOPLASTIC ELASTOMER



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Cables & Cords
Model	233

## Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SJEOOW

## Packaging

Carton	1
Weight Per foot	0.086

## Uses, Certifications, and Standards

Application	Industrial Control, Motor Control, Mining, Portable Power Distribution, Pushbutton Remote Control, Robotic System, Stage Equipment, Lighting
Approval	UL 62, CSA C22.2, MSHA
Temperature Rating	-50 TO 105 DEG C