



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

706 Solon Rd.
75165-0000, TX Waxahachie
Phone: 972-937-6965
Fax: 972-937-6968



SHC1021 Cord Conn, STR ML, .19-.25", 1/2", Alum *Hubbell Wiring Devices*

Catalog Number	SHC1021
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Cord Connectors, Straight Male, .19"-.25", 1/2", Aluminum
Weight per unit	0.0140 (lbs/each)
Product Category	Cable & Cord Grips

Features

Number of Conductors	Single
pallet quantity	13500

Material, Color, and Finish

Color	Metallic
Color Code	RED

Dimensions and Weight

Size	1/2" NPT
------	----------

Descriptions

Description	CORD CONN, STR ML, .19-.25", 1/2", ALUM
extra long description	HWDK SHC1021 CORD CONN, STR ML, .19
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from 1/4" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth
Long Description	Kellems Wire Management, Cord Connectors, Straight Male, .19"-.25", 1/2", Aluminum
Product Type	Cord Conn, STR ML, .19-.25", 1/2", Alum
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585200217
Manufacturers Part Number	SHC1021
series	Standard Duty
UPC	783585200217



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

706 Solon Rd.
75165-0000, TX Waxahachie
Phone: 972-937-6965
Fax: 972-937-6968

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	STRAIGHT MALE

Packaging

Carton	1
Package	50
Weight Per each	0.014

Uses, Certifications, and Standards

Application	Straight Male- Form 2
environmental conditions	Suitable for use in wet locations when used with a listed nylon washer between box and fitting.
Mounting	Locknut or Tapped Opening
nema rating	12;13;4;4X
standard	UL Listed