



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP264I 4G STD Deco PLT *Pass & Seymour/Legrand*

| | |
|------------------|------------------------|
| Catalog Number | SP264I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | |
| Weight per unit | 0.1750 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-------------|---------------|
| gang | 4 in |
| insulation | None IN |
| Material | THERMOPLASTIC |
| orientation | Vertical |

Dimensions and Weight

| | |
|-----------|-------|
| Size | 5" IN |
| Thickness | .30" |

Descriptions

| | |
|------------------|---|
| Description | 4G STD DECO PLT |
| Product Type | Plate Plastic 4G 4SPLEX W/Out Line I |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007680126 |
| Manufacturers Part Number | SP264-I |
| sub brand | Pass & Seymour |
| UPC | 785007680126 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging


| | |
|-----------------|-------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.175 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL 514 |

DECORATOR OPENINGS, FOUR GANG, IVORY

SP264I | [Pass & Seymour](#)



FEATURES & BENEFITS

Plate Plastic 4gang 4sierraplex Without Line Ivory



- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent, and moisture.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Size: Standard
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121704
UR: No

DIMENSIONS

Weight: 0.17095

TECHNICAL INFORMATION

Material: Thermoset Plastic

Capacity: 4-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

