

Specifications



Photo is representative



Eaton SPD3K0400

Eaton NEMA 1 Surface mount, Accepts PD3, 3-Pole, 400A frame MCCB

General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	SPD3K0400
UPC	786689661861
PRODUCT LENGTH/DEPTH	15.4 in
PRODUCT HEIGHT	42.3 in
PRODUCT WIDTH	14.1 in
PRODUCT WEIGHT	65 lb
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Power Defense Enclosure - not approved for Series C/G MCCB
GLOBAL CATALOG	SPD3K0400



Powering Business Worldwide

Product specifications

AMPERAGE RATING	400 A
ENCLOSURE	NEMA 1
MOUNTING METHOD	Surface mounting
NUMBER OF POLES	Three-pole
TYPE	CIRCUIT BREAKER ENCLOSURE

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SPD3K0400
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton SPD3K0400

Eaton NEMA 1 Surface mount, Accepts PD3, 3-Pole, 400A frame MCCB

General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	SPD3K0400
UPC	786689661861
PRODUCT LENGTH/DEPTH	15.4 in
PRODUCT HEIGHT	42.3 in
PRODUCT WIDTH	14.1 in
PRODUCT WEIGHT	65 lb
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Power Defense Enclosure - not approved for Series C/G MCCB
GLOBAL CATALOG	SPD3K0400



Powering Business Worldwide

Product specifications

AMPERAGE RATING	400 A
ENCLOSURE	NEMA 1
MOUNTING METHOD	Surface mounting
NUMBER OF POLES	Three-pole
TYPE	CIRCUIT BREAKER ENCLOSURE

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SPD3K0400
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

