

ROCKER SWITCHES • SMALL APPLIANCE

.550" X 1.125" PANEL CUTOUT • .250" Q.C. TERMINATION										
POLES & THROWS	CIRCUIT FUNCTIONS	NOMINAL RATING			ROCKER ACTUATOR SHAPE	ACTUATOR/ LENS COLORS	VISI-ROCKER® END COLOR/ IMPRINTING	LAMP VOLTAGE	CATALOG NUMBER	FIG. NO.
		AMPS	AMPS	H.P.						
		125 VAC	250 VAC	125-250 VAC						















MAINTAINED CONTACT

SPST	ON-OFF	12 Volts Incandescent			CURVED	AMBER/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1207-BG	1
SPST	ON-OFF	12 Volts Incandescent			CURVED	RED/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1209-BG	2
SPST	ON-OFF	15	10	3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1218-BG	3
SPST	ON-OFF	15	10	3/4	"V" STYLE	AMBER/TRANSPARENT	NONE/NONE	125V NEON	SS1225-BG	4
SPST	ON-OFF	15	10	3/4	"V" STYLE	RED/TRANSPARENT	NONE/NONE	125V NEON	SS1227-BG	5
SPST	ON-OFF	15	10	3/4	"V" STYLE	GREEN/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1229-BG	5
SPST	ON-OFF	15	10	3/4	PADDLE	BLACK/NONE	NONE/NONE	NONE	SS1230-BG	6
SPST	ON-OFF	15	10	3/4	PADDLE	BLACK/AMBER	NONE/NONE	125V NEON	SS1237-BG	7
SPST	ON-OFF	15	10	3/4	PADDLE	BLACK/RED	NONE/NONE	125V NEON	SS1239-BG	7
SPST	ON-OFF	16	10	3/4	CURVED	BLACK/NONE	RED/ON-OFF ²	NONE	SS1201-BG	8
SPST	ON-OFF	16	10	3/4	CURVED	BLACK/NONE	NONE/NONE	NONE	SS1203-BG	9
SPST	ON-OFF	16	10 ¹		CURVED	BLACK/NONE	RED/NONE	NONE	SS1202-BG	10
SPST	ON-OFF	16	10 ¹		CURVED	AMBER/TRANSPARENT	NONE/NONE	125V NEON	SS1208-BG	1
SPST	ON-OFF	16	10 ¹		CURVED	AMBER/TRANSLUCENT	NONE/NONE	125V NEON	SS1214-BG	11
SPST	ON-OFF	16	10 ¹		CURVED	RED/TRANSPARENT	NONE/NONE	125V NEON	SS1210-BG	2
SPST	ON-OFF	16	10 ¹		CURVED	RED/TRANSLUCENT	NONE/NONE	125V NEON	SS1216-BG	12
SPDT	ON-ON	15	10	3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1221-BG	13
SPDT	ON-ON	16	10	3/4	CURVED	BLACK/NONE	NONE/NONE	NONE	SS1205-BG	14
SPDT	ON-OFF-ON	15	10	3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1223-BG	13
SPDT	ON-OFF-ON	16	10		CURVED	BLACK/NONE	NONE/NONE	NONE	SS1206-BG	14

¹ 10 (4) Amps 250 VAC μ 185

² On-Off same color as Visi (Red)

continued on page 2



★ Switch height measurement in Figures above, includes body and terminals combined



All specifications and dimensions are for reference only. If specific information is needed and/or of critical nature, contact Selecta Products headquarters for specific information before ordering.

ROCKER SWITCHES • SMALL APPLIANCE

.550" X 1.125" PANEL CUTOUT • .250" Q.C. TERMINATION										
POLES & THROWS	CIRCUIT FUNCTIONS	NOMINAL RATING			ROCKER ACTUATOR SHAPE	ACTUATOR/ LENS COLORS	VISI-ROCKER® END COLOR/ IMPRINTING	LAMP VOLTAGE	CATALOG NUMBER	FIG. NO.
		AMPS	AMPS	H.P.						
		125 VAC	250 VAC	125-250 VAC						















MAINTAINED CONTACT

SPST	ON-OFF	12 Volts Incandescent	CURVED	AMBER/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1207-BG	1
SPST	ON-OFF	12 Volts Incandescent	CURVED	RED/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1209-BG	2
SPST	ON-OFF	15 10 3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1218-BG	3
SPST	ON-OFF	15 10 3/4	"V" STYLE	AMBER/TRANSPARENT	NONE/NONE	125V NEON	SS1225-BG	4
SPST	ON-OFF	15 10 3/4	"V" STYLE	RED/TRANSPARENT	NONE/NONE	125V NEON	SS1227-BG	5
SPST	ON-OFF	15 10 3/4	"V" STYLE	GREEN/TRANSPARENT	NONE/NONE	12V INCANDESCENT	SS1229-BG	5
SPST	ON-OFF	15 10 3/4	PADDLE	BLACK/NONE	NONE/NONE	NONE	SS1230-BG	6
SPST	ON-OFF	15 10 3/4	PADDLE	BLACK/AMBER	NONE/NONE	125V NEON	SS1237-BG	7
SPST	ON-OFF	15 10 3/4	PADDLE	BLACK/RED	NONE/NONE	125V NEON	SS1239-BG	7
SPST	ON-OFF	16 10 3/4	CURVED	BLACK/NONE	RED/ON-OFF ²	NONE	SS1201-BG	8
SPST	ON-OFF	16 10 3/4	CURVED	BLACK/NONE	NONE/NONE	NONE	SS1203-BG	9
SPST	ON-OFF	16 10 ¹	CURVED	BLACK/NONE	RED/NONE	NONE	SS1202-BG	10
SPST	ON-OFF	16 10 ¹	CURVED	AMBER/TRANSPARENT	NONE/NONE	125V NEON	SS1208-BG	1
SPST	ON-OFF	16 10 ¹	CURVED	AMBER/TRANSLUCENT	NONE/NONE	125V NEON	SS1214-BG	11
SPST	ON-OFF	16 10 ¹	CURVED	RED/TRANSPARENT	NONE/NONE	125V NEON	SS1210-BG	2
SPST	ON-OFF	16 10 ¹	CURVED	RED/TRANSLUCENT	NONE/NONE	125V NEON	SS1216-BG	12
SPDT	ON-ON	15 10 3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1221-BG	13
SPDT	ON-ON	16 10 3/4	CURVED	BLACK/NONE	NONE/NONE	NONE	SS1205-BG	14
SPDT	ON-OFF-ON	15 10 3/4	"V" STYLE	WHITE/NONE	NONE/NONE	NONE	SS1223-BG	13
SPDT	ON-OFF-ON	16 10	CURVED	BLACK/NONE	NONE/NONE	NONE	SS1206-BG	14

¹ 10 (4) Amps 250 VAC μ 185

² On-Off same color as Visi (Red)

continued on page 2



★ Switch height measurement in Figures above, includes body and terminals combined



All specifications and dimensions are for reference only. If specific information is needed and/or of critical nature, contact Selecta Products headquarters for specific information before ordering.