



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPK110 Speaker & Fan *Broan/Nutone LLC*

Catalog Number	SPK110
Manufacturer	Broan/Nutone LLC
Description	Bath and Ventilation Speaker Fan, Ceiling Type; 11-3/8 Inch Length X 10-1/2 Inch Width X 7-3/4 Inch Height Size; UL, UL (Canada and US) Approval; 0.9 Amp Current Rating; Rugged Galvanized Steel Housing Material; 110 CFM Air Flow Rate
Weight per unit	12.1 (lbs/each)
Product Category	Exhaust Fan Parts & Accy.

Features

Air Flow Rate	110 CFM
Current Rating	0.9 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White Polymeric
Grill Shape	Rectangular
Grill Size	13 Inch Length x 14 Inch Width
Housing Shape	Rectangular
Sound Level	1 SONES

Material, Color, and Finish

Housing Material	Rugged Galvanized Steel
------------------	-------------------------

Dimensions and Weight

Size	11-3/8 Inch Length x 10-1/2 Inch Width x 7-3/4 Inch Height
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Power Rating 31.4 Watt; Includes Speaker
Commodity Description	Exhaust Fan Parts & Accessories
Description	SPEAKER & FAN
extra long description	CEILING TYPE; 11-3/8 INCH LENGTH X 10-1/2 INCH WIDTH X 7-5/8 INCH HEIGHT SIZE; UL (CANADA AND US), HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.9 AMP CURRENT RATING; GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1 SONES SOUND LEVEL; 13 INCH LENGTH X 14 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 105 SQUARE FOOT VENTILATION AREA; SENSONIC[R], BLUETOOTH[R] BRAND; POWER RATING 31.4
Long Description	BATH AND VENTILATION SPEAKER FAN, CEILING TYPE; 11-3/8 INCH LENGTH X 10-1/2 INCH WIDTH X 7-3/4 INCH HEIGHT SIZE; UL, UL (CANADA AND US) APPROVAL; 0.9 AMP CURRENT RATING; RUGGED GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE
Product Type	Bath and Ventilation Speaker Fan

Manufacturer Information

Brand	BROAN
GTIN	00026715234127
Manufacturers Part Number	SPK110
UPC	026715234127

Taxonomies, Classifications, and Categories

Category Description	CEILING FANS AND ACCESSORIES
Type	CEILING

Packaging

Carton	1
Weight Per each	12.05

Uses, Certifications, and Standards

Approval	UL, UL (CANADA AND US)
----------	------------------------