



Southwire™

TOOLS & EQUIPMENT

QWIKline™ LINE EXPANSION

We've expanded our line of Southwire QWIKtape™ Pull Tape with 21 new skus! This expansion includes various new sizes and types with varying breaking strengths. For 1250 lb., 1800 lb., and 2500 lb. pulls tapes we will have lengths of 500', 1000', 1500', and 5000'. We have also added 3000' reels of detectable QWIKtape™ in 1250 lb., 1800 lb., and 2500 lb! Detectable pull tape has a small copper wire run through the length. When a charge is added to it an underground cable detecting wand can be used to find runs of buried non-metallic conduit once the tape is blown through!

THREAD AND MEASURE CONDUIT

QUICK AND ACCURATE

EASY-TO-READ FOOTAGE MARKINGS

LOW COEFFICIENT OF FRICTION

NEW DETECTABLE PULL TAPE



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



QWIKline™ LINE EXPANSION

SW Model Number	Description	Reel Dimensions	UPC	Pallet Quantity	Avg. Breaking Strength
SWQT1250-500S	1250 lb, 500', metal reel	10" x 5" metal		128	1250 lbs.
SWQT1250-1000S	1250 lb, 1000' metal reel	10" x 5" metal		128	1250 lbs.
SWQT1250-1500S	1250 lb, 1500', metal reel	10" x 7" metal		96	1250 lbs.
SWQT1250-5000S	1250 lb, 5000', plastic reel			18	1250 lbs.
SWDQT1250-3000S	1250 lb, 3000' Detectable			36	1250 lbs.
NEW					
SWQT1800-500S (NEW)	1800 lb, 500', metal reel	10" x 5" metal		128	1800 lbs.
SWQT1800-1000S (NEW)	1800 lb, 1000' metal reel	10" x 5" metal		128	1800 lbs.
SWQT1800-1500S (NEW)	1800 lb, 1500', metal reel	10" x 7" metal		96	1800 lbs.
SWQT1800-5000S (NEW)	1800 lb, 5000', plastic reel			12	1800 lbs.
SWDQT1800-3000S (NEW)	1800 lb, 3000' Detectable			36	1800 lbs.
NEW					
SWQT2500-500S (NEW)	2500 lb, 500', metal reel	10" x 7" metal		96	2500 lbs.
SWQT2500-1000S (NEW)	2500 lb, 1000' metal reel	10" x 7" metal		96	2500 lbs.
SWQT2500-1500S (NEW)	2500 lb, 1500', metal reel	10" x 10" metal		64	2500 lbs.
SWQT2500-5000S (NEW)	2500 lb, 5000', plastic reel			12	2500 lbs.
SWQT2500-6000S (NEW)	2500 lb, 6000', plywood reel			18	2500 lbs.
SWDQT2500-3000S (NEW)	2500 lb, 3000' Detectable			36	2500 lbs.
NEW					
PL2200 (NEW)	2,220' 500 LBS Tensile Strength Poly Line			36	500 lbs.
PL6500	POLY,LINE 6500' 210 TENSILE STRENGTH			36	210 lbs.
PL500	POLY, LINE 500' 210 TENSILE STRENGTH			N/A	210 lbs.
NEW					
SWCMT160-3000S	CNDUIT MEASURING TAPE 160LB 3000FT SPOOL			144	160 lbs.
SWMT400-4500P	POLYESTER MULE TAPE 400LB 4500FT PAIL			36	400 lbs.
SWMT1250-3000S	POLYESTER MULE TAPE 1250LB 3000FT SPOOL			36	1250 lbs.
SWMT1800-3000S	POLYESTER MULE TAPE 1800LB 3000FT SPOOL			36	1800 lbs.
SWMT2500-3000S	POLYESTER MULE 2500LB 3000FT SPOOL			36	2500 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.