

# Eaton T20P11S2516

Catalog Number: T20P11S2516

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 220°C, 25 kVA, upright only , Single-phase, 240X480V, 120Y/240 Vac, NEMA ST-20, 1 at +5%, 150°C, 25 kVA, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, DOE 2016



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	T20P11S2516
	<b>UPC</b>
	786680147623
<b>Product Length/Depth</b>	<b>Product Height</b>
17 in	33.5 in
<b>Product Width</b>	<b>Product Weight</b>
22.5 in	236 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	10 CFR Part 431 (2016) Efficient

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Frame

FR842A

### Insulation

220 °C

### Mounting

Floor or wall, upright only

### Tap size

1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%

### Type

Energy-efficient ventilated type DS-3 transformer

### Wiring connection

3XA

## Miscellaneous

### Weathershield

WS45A

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

25 kVA

### Primary voltage

240 V, 480 V

### Secondary Voltage

120Y/240 V

### Sound Level

NEMA ST-20

### Temperature rise

150 °C rise

### Volt ampere rating

25 kVA

### Voltage rating

240 X 480 Vac-120Y/240 Vac

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T20P11S2516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)