



T25FC0 1/4" BLK Spiral Wrap, 100' Roll

Panduit Corporation

Catalog Number	T25FC0
Manufacturer	Panduit Corporation
Description	The T25F-C0 Polyethylene Spiral Wrap Provides Continuous Abrasion Protection For Wires, Cables, and Tubing. The Spiral Wrap Harnesses Multiple Cables Into A Single Manageable Bundle While Allowing For Breakouts. Lightweight, Flexible, Durable Protection Allows For Use With Irregular Shapes. Rated For Use Up to 122°F (50°C). 0.25" (6.4 MM) Diameter X 100' (30.5 M) Long. Bundle Diameter Range 0.1875" to 2" (4.8 MM to 50.8 MM). Color Black.
Weight per unit	1.8 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Material	Polyethylene
maximum bundle diameter	2
media	Yes
minimum bundle diameter	0.1875
outside diameter	0.25
Wall Thickness	0.04

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	1/4" BLK SPIRAL WRAP, 100' ROLL
extra long description	PAN T25F-C0 T25F-C0 Spiral Wrap, Bl
Long Description	The T25F-C0 Polyethylene Spiral Wrap provides continuous abrasion protection for wires, cables, and tubing. The spiral wrap harnesses multiple cables into a single manageable bundle while allowing for breakouts. Lightweight, flexible, durable protection allows for use with irregular shapes. Rated for use up to 122°F (50°C). 0.25" (6.4 mm) diameter x 100' (30.5 m) long. Bundle Diameter Range 0.1875" to 2" (4.8 mm to 50.8 mm). Color Black.
Product Type	T25F-C0 Spiral Wrap, Black, Uv Pe, 0.1875" Min Dia., 100' Ro



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road
76426-0000, TX Bridgeport
Phone: 940-683-5740
Fax: 940-683-5299

Manufacturer Information

Brand	PANDUIT
GTIN	00074983705559
Manufacturers Part Number	T25F-C0
UPC	074983705559

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Spiral Wrap

Packaging

Carton	1
Weight Per roll	1.8

Uses, Certifications, and Standards

Application	Harness Multiple Cables Into a Single Manageable Bundle; Allows Breakouts of Single/Multiple Cables; Provides Abrasion Protection for Wire, Cables, Hoses, and Tubing
standard	UL Recognized - E141152; UL94HB
Temperature Rating	122