



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue  
75672-0000, TX Marshall  
Phone: 903-935-9535  
Fax: 903-935-3490



## T58 1-1/2" Cond Body *Appleton/Oz Gedney*

Catalog Number	T58
Manufacturer	Appleton/Oz Gedney
Description	FM8 Grayloy-Iron Unilets Type T Conduit Outlet Body, Hub Size: 1-1/2 In, Form: 8, Length: 10.38 In, Width: 4.03 In, Height: 2.78 In, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coat), Color: Gray,
Weight per unit	5.7 (lbs/each)
Product Category	Bodies & Covers

### Features

connection	Tapered Female Threaded
Form	8

### Material, Color, and Finish

Color	Gray
Finish	Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat)

### Dimensions and Weight

Height	2.78
Hub Size	1-1/2
Length	10.38
Width	4.03

### Descriptions

Description	1-1/2" COND BODY
extra long description	APP T58 1-1/2 TYPE T FORM 8 BODY
Long Description	FM8 Grayloy-Iron UNILETS Type T Conduit Outlet Body, Hub Size: 1-1/2 IN, Form: 8, Length: 10.38 IN, Width: 4.03 IN, Height: 2.78 IN, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat), Color: Gray,
Product Type	1-1/2 Type T Form 8 Body
Special Features	Accurately tapped, tapered threads for tight, rigid joints and excellent ground continuity;Allow connections for branch runs;Completely interchangeable with Crouse-Hinds Form 8 bodies, gaskets and covers;Connect and change direction of conduit runs;Equivalent FM8 and Form 8 units have identical applications and installation dimensions;Fits flush and snug against flat surfaces for more stable installation;Flat back design provides greater cubic content for easier wire pulling and more room for splicing;Make



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue  
75672-0000, TX Marshall  
Phone: 903-935-9535  
Fax: 903-935-3490

## Manufacturer Information

Brand	Appleton
GTIN	00781381744355
UPC	781381744355

## Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Type T Conduit Outlet Body

## Packaging

Carton	1
Package	5
Weight Per each	5.65

## Uses, Certifications, and Standards

Application	For Use With Rigid Steel Conduit And IMC
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1