

Specifications

Eaton T87 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 3"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T87 SA
UPC	782274364919
PRODUCT LENGTH/DEPTH	12.06 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	4.85 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - T87 SA](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Product specifications

SHAPE	T
TRADE SIZE	3"
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton T87 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 3"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T87 SA
UPC	782274364919
PRODUCT LENGTH/DEPTH	12.06 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	4.85 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - T87 SA](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Product specifications

SHAPE	T
TRADE SIZE	3"
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

