


Specifications



Eaton TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity

General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series switch box |
| CATALOG NUMBER | TP171 |
| UPC | 786189101713 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.5 in |
| PRODUCT WEIGHT | 0.73 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------|
| DEPTH | 2-1/2" |
| TYPE | Gangable |
| CAPACITY | 12.5 cubic in |
| CONDUIT/CABLE | NM clamps |
| BRACKET STYLE | VP, Set 1/2" |
| END KNOCKOUTS | (1) 1/2 in |
| SIDE KNOCKOUTS | (1) 1/2 in |
| BOTTOM KNOCKOUTS | (1) 1/2 in |
| CABLE KNOCKOUTS | 2 |
| MATERIAL | Steel |

Resources

| | |
|-------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes Canadian certification Steel Switch Boxes UL certification |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - TP171 Steel Outlet Boxes for Electrical Systems |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:




Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity

General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series switch box |
| CATALOG NUMBER | TP171 |
| UPC | 786189101713 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.5 in |
| PRODUCT WEIGHT | 0.73 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------|
| DEPTH | 2-1/2" |
| TYPE | Gangable |
| CAPACITY | 12.5 cubic in |
| CONDUIT/CABLE | NM clamps |
| BRACKET STYLE | VP, Set 1/2" |
| END KNOCKOUTS | (1) 1/2 in |
| SIDE KNOCKOUTS | (1) 1/2 in |
| BOTTOM KNOCKOUTS | (1) 1/2 in |
| CABLE KNOCKOUTS | 2 |
| MATERIAL | Steel |

Resources

| | |
|-------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes Canadian certification Steel Switch Boxes UL certification |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - TP171 Steel Outlet Boxes for Electrical Systems |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.