



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMRP5101 10-Function Time Delay Relay SPDT 12A 12-240V

Eaton Corp

Catalog Number	TMRP5101
Manufacturer	Eaton Corp
Description	TMRP Series Timing Relay, Octal Style Terminals, 8 Pins, Control Switch Trigger, 0.1 Seconds-9, 990 Hours Time Delay, 12-240 Vac/DC Input Voltage, On/Off Delay, 90% Silver, 10% Nickel, 12A Contact Rating, SPDT Contact Configuration
Weight per unit	0.3000 (lbs/each)
Product Category	Timing Relays & Accessories

Features

Contact Configuration	SPDT
Contact Rating	12A
dimensions	3.4600 IN X 1.8800 IN X 1.8800 IN
Number of Pins	8

Descriptions

Description	10-FUNCTION TIME DELAY RELAY SPDT 12A 12-240V
extra long description	ETN TMRP5101 10-function TD rl, SPD
Features	Universal TR series, TMRP, TMR and E5-248 timing relays combine flexibility with ease of use and installation, while compact designs save panel space. With multiple mount options, models, a wide range of input voltage, timing range and functionality, there are versatile timing relays to meet any timing requirements.
Long Description	TMRP Series Timing Relay, Octal style terminals, 8 pins, Control switch trigger, 0.1 seconds-9,990 hours time delay, 12-240 Vac/dc input voltage, ON/OFF delay, 90% silver, 10% nickel, 12A contact rating, SPDT contact configuration
Product Type	10-Function TD RL, SPDT, 12A, 12-240V

Manufacturer Information

Brand	Eaton
GTIN	00786685215365
Manufacturers Part Number	TMRP5101
UPC	786685215365

Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	Timing relay

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

standard

UL Listed,CE Marked,RoHS Compliant