Pass and Seymour

**Combination Openings, 1 Toggle Switch and 1 Blank, Two Gang, Brown**

Part No. TP113



Trademaster Plate 2-Gang 1toggle 1 Blank

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007275261 |
| Country Of Origin | Mexico | Material | Nylon |
| Wall Plate Type | Blank, Combination, Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | Limited Lifetime Warranty |
| Type | Wall Plate | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 4.75 in | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in | | |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 143222 | cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Cutout | Toggle and Blank | Thickness | 0.07 in |
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
| Mounting Type | Exposed Screws | Orientation | Horizontal |

Pass and Seymour

**Combination Openings, 1 Toggle Switch and 1 Blank, Two Gang, Brown**

Part No. TP113



Trademaster Plate 2-Gang 1toggle 1 Blank

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007275261 |
| Country Of Origin | Mexico | Material | Nylon |
| Wall Plate Type | Blank, Combination, Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | Limited Lifetime Warranty |
| Type | Wall Plate | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 4.75 in | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in | | |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 143222 | cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Cutout | Toggle and Blank | Thickness | 0.07 in |
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
| Mounting Type | Exposed Screws | Orientation | Horizontal |