

Specifications



Eaton TP256

Eaton Crouse-Hinds series Octagon Outlet Box, (1) 1/2", 3-1/2", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 9.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP256
UPC	786189102567
PRODUCT LENGTH/DEPTH	3.25 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	0.41 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	3-1/2"
DEPTH	1-1/2"
CAPACITY	9 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(4) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS [Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)
[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP256](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton TP256

Eaton Crouse-Hinds series Octagon Outlet Box, (1) 1/2", 3-1/2", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 9.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP256
UPC	786189102567
PRODUCT LENGTH/DEPTH	3.25 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	0.41 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	3-1/2"
DEPTH	1-1/2"
CAPACITY	9 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(4) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS [Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)
[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP256](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.