

Specifications

Eaton TP356



Eaton Crouse-Hinds series Adjustable Bar Hanger, Steel, Not fan rated, 16"

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series adjustable bar hanger |
| CATALOG NUMBER | TP356 |
| UPC | 786189103564 |
| PRODUCT LENGTH/DEPTH | 22.5 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.41 lb |

Certifications and compliances

| | |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------|---------------|
| STUD SPACING | 16" |
| MATERIAL | Steel |
| SPECIAL FEATURES | Not fan rated |

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP356](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton TP356



Eaton Crouse-Hinds series Adjustable Bar Hanger, Steel, Not fan rated, 16"

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series adjustable bar hanger |
| CATALOG NUMBER | TP356 |
| UPC | 786189103564 |
| PRODUCT LENGTH/DEPTH | 22.5 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.41 lb |

Certifications and compliances

| | |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------|---------------|
| STUD SPACING | 16" |
| MATERIAL | Steel |
| SPECIAL FEATURES | Not fan rated |

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP356](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

