

Specifications



Eaton TP413

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 3/4", 4", Conduit (no clamps), Welded, 3-1/2", Steel, (8) 1/2", (1) 3/4" C, (4) 3/4", (4) 1", 50.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP413
UPC	786189104134
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	1.28 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	50 cubic in
DEPTH	3-1/2"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 1/2 in, (1) 3/4 in C, (4) 3/4 in, (4) 1 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - TP413](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP413

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 3/4", 4", Conduit (no clamps), Welded, 3-1/2", Steel, (8) 1/2", (1) 3/4" C, (4) 3/4", (4) 1", 50.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP413
UPC	786189104134
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	1.28 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	50 cubic in
DEPTH	3-1/2"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 1/2 in, (1) 3/4 in C, (4) 3/4 in, (4) 1 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - TP413](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

