


# Specifications



## Eaton TP432VMS

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", 30.3 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP432VMS
<b>UPC</b>	662279001210
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	1 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>BOX SIZE</b>	4"
<b>CAPACITY</b>	30.3 cubic in
<b>DEPTH</b>	2-1/8"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>BRACKET STYLE</b>	VMS
<b>CONSTRUCTION</b>	Welded
<b>SIDE KNOCKOUTS</b>	(8) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page</a>
CERTIFICATION REPORTS	<a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification</a> <a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP432VMS</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**




**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP432VMS

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", 30.3 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP432VMS
<b>UPC</b>	662279001210
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	1 lb



*Powering Business Worldwide*

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>BOX SIZE</b>	4"
<b>CAPACITY</b>	30.3 cubic in
<b>DEPTH</b>	2-1/8"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>BRACKET STYLE</b>	VMS
<b>CONSTRUCTION</b>	Welded
<b>SIDE KNOCKOUTS</b>	(8) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page</a>
CERTIFICATION REPORTS	<a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification</a> <a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP432VMS</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.