

# Specifications



## Eaton TP557

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", VS, Conduit (no clamps), Drawn, 2-1/8", Steel, (5) 1/2", (4) 1/2", (1) 3/4" C, 42.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP557
<b>UPC</b>	786189105575
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	1.2 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>BOX SIZE</b>	4-11/16"
<b>CAPACITY</b>	42 cubic in
<b>DEPTH</b>	2-1/8"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>BRACKET STYLE</b>	VS
<b>CONSTRUCTION</b>	Drawn
<b>SIDE KNOCKOUTS</b>	(5) 1/2 in, (4) 1/2 in, (1) 3/4 in C
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds TP557 3D drawing](#)

**CATALOGS** [Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

**CERTIFICATION REPORTS** [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - TP557](#)  
[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.