Pass and Seymour
**TradeMaster® Jumbo 3-Gang Nylon Wall Plate, 3 Toggle Switch Openings, White**
Part No. TPJ3W



Trademaster Wall Plate Jumbo 3 Gang 3 Toggle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

For covering patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007025385 |
| Country Of Origin | Mexico | Material | Nylon |
| Construction | Plastic | Wall Plate Size | Trademaster Jumbo |
| Wall Plate Type | Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | 1-Year Limited Warranty |
| Type | Wall Plate | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 6.9375 in | Product Depth US | 0.25 in |
| Product Height US | 5.0625 in | | |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 143222 | cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Thickness | 0.07 in | Number of Gangs | 3 |
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
| Orientation | Vertical | | |

Pass and Seymour
**TradeMaster® Jumbo 3-Gang Nylon Wall Plate, 3 Toggle Switch Openings, White**
Part No. TPJ3W



Trademaster Wall Plate Jumbo 3 Gang 3 Toggle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

For covering patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007025385 |
| Country Of Origin | Mexico | Material | Nylon |
| Construction | Plastic | Wall Plate Size | Trademaster Jumbo |
| Wall Plate Type | Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | 1-Year Limited Warranty |
| Type | Wall Plate | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 6.9375 in | Product Depth US | 0.25 in |
| Product Height US | 5.0625 in | | |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 143222 | cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Thickness | 0.07 in | Number of Gangs | 3 |
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
| Orientation | Vertical | | |