



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.
72023-0000, AR Cabot
Phone: 501-605-1780
Fax: 501-605-1785



TRAFGF15B Af/GF TR Duplex 15A 125V BR

Eaton Wiring Devices

Catalog Number	TRAFGF15B
Manufacturer	Eaton Wiring Devices
Description	Eaton Afgf Receptacle, Tamper Resistant, Self-Test, #14 - 10 Awg, 15A, Residential, Commercial, Flush, 125 V, Afgf, Back and Side Wire, Brown, Brass, Receptacle, Tamper Resistant, Polycarbonate, 5-15R, Two-Pole, Three-Wire, Grounding
Weight per unit	0.4010 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15A
dimensions	2.8150 IN X 2.0100 IN X 4.6250 IN
media	Yes
Voltage Rating	125V

Descriptions

Description	AF/GF TR DUPLEX 15A 125V BR
extra long description	EWD TRAFGF15B AF/GF TR Duplex 15A 1
Features	Eaton's Slim Dual Function Arc Fault/Ground Fault (AF/GF) receptacles are designed with quick installation, ease-of-use and safety in mind. The updated design offers the slimmest in-box depths on the market that allows for easy installation, crisp design that is visually appealing and intuitive, and compliance with the latest UL and NEC safety standards. Eaton's AF/GF receptacles are a great alternative to AF/GF breakers where local reset is desired.
Long Description	Eaton AFGF receptacle, Tamper resistant, Self-test, #14 - 10 AWG, 15A, Residential, Commercial, Flush, 125 V, AFGF, Back and side wire, Brown, Brass, Receptacle, Tamper resistant, Polycarbonate, 5-15R, Two-pole, three-wire, grounding
Product Type	Af/GF TR Duplex 15A 125V BR
Special Features	15A AFCI

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664747557
Manufacturers Part Number	TRAFGF15B
UPC	032664747557

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	AFGF receptacle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.
72023-0000, AR Cabot
Phone: 501-605-1780
Fax: 501-605-1785

Availability

Status Inactive

Packaging

Carton 10

Package 40

Weight Per each 0.401

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other

environmental conditions Tamper resistant

standard UL Listed,NOM,CSA Certified,cULus Listed