



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.  
76504-0000, TX Temple  
Phone: 254-899-2800  
Fax: 254-899-2805



## TR5262USBW Duplex Recp 15A TR Spec W/3.1A Usb Charge WH

*Pass & Seymour/Legrand*

|                  |                                                                                                                                                                                                                                                                                                                            |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | TR5262USBW                                                                                                                                                                                                                                                                                                                 |
| Manufacturer     | Pass & Seymour/Legrand                                                                                                                                                                                                                                                                                                     |
| Description      | Designed For Commercial Markets With Strength and Durability In Mind, This Combination Duplex Receptacle and Two Usb Type-A Features 3.1A Overall Usb Charging Capability and Is Compatible With Usb 2.0 & 3.0 Devices. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page. |
| Weight per unit  | 0.3392 (lbs/each)                                                                                                                                                                                                                                                                                                          |
| Product Category | Combination Devices                                                                                                                                                                                                                                                                                                        |

### Features

|                     |                                |
|---------------------|--------------------------------|
| amperage rating     | 15                             |
| connection          | Side & Back Wired              |
| Dielectric Strength | Withstands 2000V minimum       |
| indoor/outdoor      | Indoor                         |
| Number of Wires     | 3                              |
| Outlet Type         | Tamper-Resistant, USB-Charging |
| Phase               | 1                              |
| Poles               | 2                              |
| Voltage             | 125.0 V                        |
| Voltage Rating      | 125                            |
| Wall Plate Included | NO                             |
| Wire Size           | 14 - 10                        |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|        |       |
|--------|-------|
| Depth  | 1.392 |
| Height | 3.281 |
| Width  | 1.693 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.  
76504-0000, TX Temple  
Phone: 254-899-2800  
Fax: 254-899-2805

## Descriptions

|                        |                                                                                                                                                                                                                                                                                                                            |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | DUPLEX RECP 15A TR SPEC W/3.1A USB CHARGE WH                                                                                                                                                                                                                                                                               |
| extra long description | P&S TR5262USBW DUP REC 15A TR SPEC                                                                                                                                                                                                                                                                                         |
| Features               | Single Piece Plated Steel Mounting Strap, USB-A Charging                                                                                                                                                                                                                                                                   |
| Long Description       | Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page. |
| Product Type           | Dup Rec 15A TR Spec W/3.1A Usb CHRG W                                                                                                                                                                                                                                                                                      |
| Special Features       | Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.                                                                                                           |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007031621         |
| Manufacturers Part Number | TR-5262USBW            |
| UPC                       | 785007031621           |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type                 | Outlet                            |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 50     |
| Weight Per each | 0.3392 |

## Uses, Certifications, and Standards

|                          |                             |
|--------------------------|-----------------------------|
| Application              | Commercial                  |
| environmental conditions | UL94 V2                     |
| Mounting                 | BOX                         |
| nema rating              | 5-20R                       |
| standard                 | UL, CULUS, FEDSPEC, FEDSPEC |