PASS & SEYMOUR®
Recessed TV Boxes
New Work

TV2MW

New Work Recessed TV Frame & Box Mounting Bracket for Steel or Wood Studs

The TV2MW New Work Boxes are aimed at new commercial construction projects. The two-gang boxes are constructed from factory-assembled steel and contain and integral 35 cubic inch electrical box. They come with an adjustable trim ring that is suitable for various thicknesses of wall board. There is no field assembly required. The boxes are designed to provide a snug-to-wall placement for new-work applications in the hospitality, education, commercial, and residential environments. They are ideal for flat-screen TVs and reducing the clutter associated with a variety of cabling. Plugs and multimedia connections are conveniently recessed behind the wall surface.



FEATURES & BENEFITS

Supports one line voltage device and up to 6 low-voltage connectors or pass-thru brush.

35 cubic inch integral metal box with concentric 1/2" & 3/4" knockouts that accept MC, AC, Romex, or conduit.

Low voltage side has 1 1/4" knockouts.

Fits in standard 2 x 4 or 2 x 6 construction.

Polycarbonate trim ring cover.



TV2MW

All-steel Construction with powder-coat paint finish.

Adjustable for 1/2" to 1 1/4" wall board.

cULus Listed.

Ratings are a permanent part of the device.

Tri-drive green ground screw with green chromate.

Side mount or face mount works on either side of steel studs.


FIELD USES/VERTICAL MARKETS

- Single Family Home
- Education
- Multiple Dwelling
- Hospitality
- Retail/Office

PASS & SEYMOUR®
Recessed TV Boxes
New Work

TECHNICAL INFORMATION

Catalog Number	Description	Cubic Inches	Length.	Width	Height	Wire Fill
New Work TV Recessed Box & Frame						
TV2MW	New Work Metal Television Box 2 Gang	35	6.9	7.6	3.5	17 No. 4 15 No. 12 14 No. 10





Back side view of TV2MW

ALSO AVAILABLE...

- Hospital Grade Devices
- PlugTail™ Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips

Electrical Wiring Systems
P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone:905.738.9195
www.legrand.ca

SF20140 – December 2013 – For latest specs visit www.legrand.us/passandseymour

© Copyright 2013 All Rights Reserved Legrand EWS/CGXTP

PASS & SEYMOUR®
Recessed TV Boxes
New Work

TV2MW

New Work Recessed TV Frame & Box Mounting Bracket for Steel or Wood Studs

The TV2MW New Work Boxes are aimed at new commercial construction projects. The two-gang boxes are constructed from factory-assembled steel and contain and integral 35 cubic inch electrical box. They come with an adjustable trim ring that is suitable for various thicknesses of wall board. There is no field assembly required. The boxes are designed to provide a snug-to-wall placement for new-work applications in the hospitality, education, commercial, and residential environments. They are ideal for flat-screen TVs and reducing the clutter associated with a variety of cabling. Plugs and multimedia connections are conveniently recessed behind the wall surface.



FEATURES & BENEFITS

Supports one line voltage device and up to 6 low-voltage connectors or pass-thru brush.

35 cubic inch integral metal box with concentric 1/2" & 3/4" knockouts that accept MC, AC, Romex, or conduit.

Low voltage side has 1 1/4" knockouts.

Fits in standard 2 x 4 or 2 x 6 construction.

Polycarbonate trim ring cover.



TV2MW

All-steel Construction with powder-coat paint finish.

Adjustable for 1/2" to 1 1/4" wall board.

cULus Listed.

Ratings are a permanent part of the device.

Tri-drive green ground screw with green chromate.

Side mount or face mount works on either side of steel studs.


FIELD USES/VERTICAL MARKETS

- Single Family Home
- Education
- Multiple Dwelling
- Hospitality
- Retail/Office

PASS & SEYMOUR®
Recessed TV Boxes
New Work

TECHNICAL INFORMATION

Catalog Number	Description	Cubic Inches	Length.	Width	Height	Wire Fill
New Work TV Recessed Box & Frame						
TV2MW	New Work Metal Television Box 2 Gang	35	6.9	7.6	3.5	17 No. 4 15 No. 12 14 No. 10





Back side view of TV2MW

ALSO AVAILABLE...

- Hospital Grade Devices
- PlugTail™ Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips

Electrical Wiring Systems
P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone:905.738.9195
www.legrand.ca

SF20140 – December 2013 – For latest specs visit www.legrand.us/passandseymour

© Copyright 2013 All Rights Reserved Legrand EWS/CGXTP