



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## U50 1/4"-20X1/2" (Pipe Size) U-Bolt W/ Strap & Hex

L.H. Dottie CO.

Catalog Number	U50
Manufacturer	L.H. Dottie CO.
Description	U-Bolt, Low Carbon Steel Material, Zinc Plated Finish, 1-3/4 In. Length, 1 X 1-3/4 In. Size, Internal-1 In. Diameter, NC Rolled Machine Thread, 2 Nuts, Hex Nut Type, 1 In. Thread Length, 1-3/4 In. Height, 1/2 In. Pipe Diameter, 1/4 In. Thread Diameter
Weight per unit	2.2 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

Thread Length	1
---------------	---

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Diameter	Internal:1
Height	1-3/4
Length	1-3/4
Size	1 x 1-3/4

### Descriptions

Description	1/4"-20X1/2" (PIPE SIZE) U-BOLT W/ STRAP & HEX
extra long description	DOTTIE U50 1/2" U-Bolts Zinc Plated
Long Description	U-Bolt, Low Carbon Steel material, Zinc Plated Finish, 1-3/4 in. length, 1 x 1-3/4 in. Size, Internal-1 in. diameter, NC Rolled Machine thread, 2 nuts, Hex nut type, 1 in. thread length, 1-3/4 in. height, 1/2 in. pipe diameter, 1/4 in. thread diameter
Product Type	1/2" U-Bolts Zinc Plated With Straps and Hex Nuts
Special Features	Features: U Bolts are Generally used to Support Conduit from Strut, Provided with Hex Nuts and Plate, NC Rolled Threads

### Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002179108
UPC	781002179108

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	U-Bolt

### Packaging

Carton	25
Weight Per each	2.22



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....

Conduit .....