

# Specifications



Photo is representative

## Eaton U67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 2"

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U67
<b>UPC</b>	662276465831
<b>PRODUCT LENGTH/DEPTH</b>	17.31 in
<b>PRODUCT HEIGHT</b>	8.63 in
<b>PRODUCT WIDTH</b>	3.63 in
<b>PRODUCT WEIGHT</b>	8.85 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3 4 12

## Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds U67 3D drawing](#)

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS [IF 863 - Conduit Body Wire Pulling](#)  
[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Condulet Form 7 Industrial Grade Conduit Bodies](#)  
[Eaton Specification Sheet - U67](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Wire Fill Chart](#)  
[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Product specifications

<b>SHAPE</b>	U
<b>TRADE SIZE</b>	2"
<b>MATERIAL</b>	Feraloy iron alloy



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



Photo is representative

## Eaton U67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 2"

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U67
<b>UPC</b>	662276465831
<b>PRODUCT LENGTH/DEPTH</b>	17.31 in
<b>PRODUCT HEIGHT</b>	8.63 in
<b>PRODUCT WIDTH</b>	3.63 in
<b>PRODUCT WEIGHT</b>	8.85 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3 4 12

## Resources

<b>3D CAD DRAWING PACKAGE</b>	<a href="#">Eaton Crouse-Hinds U67 3D drawing</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 863 - Conduit Body Wire Pulling</a> <a href="#">IF 964 - Conduit Body Wire Pulling</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a> <a href="#">Eaton Specification Sheet - U67</a>
<b>TECHNICAL SERVICE BULLETINS</b>	<a href="#">Industrial Fittings Wire Fill Chart</a> <a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Product specifications

<b>SHAPE</b>	U
<b>TRADE SIZE</b>	2"
<b>MATERIAL</b>	Feraloy iron alloy



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.