

Eaton UATH7330UFLCH

Catalog Number: UATH7330UFLCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub cover plate hub mounted, 7-jaw, 3-ph, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Al, Triplex, Side-wired, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UATH7330UFLCH

UPC

782116168941

Product Length/Depth

6.5 in

Product Height

39.88 in

Product Width

20 in

Product Weight

40 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

Line

3/8 in stud

Load

3/8 in stud

Enclosure material

Aluminum

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Connection

Ground connection

Security

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Metering Equipment - Florida Meter Group \(FMG\)](#)

[Eaton Specification Sheet - UATH7330UFLCH](#)

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)