



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UB1000 Universal Bushing 1.0

Topaz - Southwire LLC

Catalog Number	UB1000
Manufacturer	Topaz - Southwire LLC
Description	Universal Bushing, Black Nylon 6/6 Material; 0.453 Inch; UL, Csa Approval; 1.063 Inch Diameter; 1000 Per Case Standard Package; Rohs Compliant; Inside Diameter 0.75 Inch; Mounting Hole Diameter 1 Inch; Thickness 0.125 Inch
Weight per unit	0.0060 (lbs/each)
Product Category	Plastic

Features

Material	Black Nylon 6/6
----------	-----------------

Dimensions and Weight

Diameter	1.063 INCH
Height	0.453 INCH

Descriptions

Additional Information	ROHS Compliant; Inside Diameter 0.75 Inch; Mounting Hole Diameter 1 Inch; Thickness 0.125 Inch
Commodity Description	Rigid Conduit Fittings - Plastic
Description	UNIVERSAL BUSHING 1.0
extra long description	UNIVERSAL TYPE; NYLON 6/6 MATERIAL; 0.453 INCH; UL, CSA APPROVAL; 1.063 INCH DIAMETER; 1000 PER CASE STANDARD PACKAGE; THICKNESS 0.125 INCH; MOUNTING HOLE DIAMETER 1 INCH; MAXIMUM INSIDE DIAMETER 0.75 INCH; COLOR BLACK
Long Description	UNIVERSAL BUSHING, BLACK NYLON 6/6 MATERIAL; 0.453 INCH; UL, CSA APPROVAL; 1.063 INCH DIAMETER; 1000 PER CASE STANDARD PACKAGE; ROHS COMPLIANT; INSIDE DIAMETER 0.75 INCH; MOUNTING HOLE DIAMETER 1 INCH; THICKNESS 0.125 INCH
Product Type	Universal Bushing

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338306608
Manufacturers Part Number	UB1000
UPC	751338306608

Taxonomies, Classifications, and Categories

Category Description	PVC ELBOWS
----------------------	------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Standard Package	1000 PER CASE
Weight Per each	0.006

Uses, Certifications, and Standards

Approval	UL, CSA
----------	---------