



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG112150 1-1/2" Ua Sealite Conduit, Bonded UL 150' *Southwire Company*

Catalog Number	UAG112150
Manufacturer	Southwire Company
Description	UL Liquid-Tuff™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1-1/2 Inch Diameter, 150 Foot Reel
Weight per unit	1.1 (lbs/each)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	1.575/1.600
Material	Steel
outside diameter	1.865/1.900

Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	150
--------	-----

Descriptions

Description	1-1/2" UA SEALTITE CONDUIT, BONDED UL 150'
extra long description	AFC 6206-35-00 1-1/2" UL LT LFMC GR
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.
Long Description	UL LIQUID-TUFF™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1-1/2 inch Diameter, 150 Foot Reel
Product Type	1-1/2" UL LT LFMC Gray 150' RL
Short Description	1-1/2" UL LT LFMC GRAY 150' RL
Special Features	UL bonded strip 3/8in - 1.25in for grounding. UL Liquidtight all sizes. Sunlight resistant. Flame retardant PVD jacket. Hot dipped zinc galvanized steel low carbon steel core.

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680148070
Manufacturers Part Number	6206-35-00
UPC	077680148070



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LFMC

Trade Size

Trade Size	1-1/2
------------	-------

Packaging

Carton	150
Weight	1.09
Weight Per each	1.13

Uses, Certifications, and Standards

Application	For Service Entrance Wiring Upto 6 FT
Temperature Rating	176