



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441



UAG4 4" Ua Sealtite Conduit, Bonded UL 25' *Southwire Company*

Catalog Number	UAG4
Manufacturer	Southwire Company
Description	TITAN2 Type UL LFMC Is Manufactured With A Spiral Wound Strip Of Heavy Gauge Corrosion-Resistant Hot-Dipped Galvanized Steel. For 3/8" Through 1-1/4" Trade Sizes The Core Is Constructed With A Square Locked Steel Strip With An Integral Copperbonding Strip Enclosed Within The Steel Convolutions. For 1-1/2" Through 4" Trade Sizes The Core Is Constructed With A Fully Interlocked Steel Strip. A Rugged Flame Retardant Flexible PVC Jacket Is Extruded Over The Steel Core. The Grey Jacket Resists Oils Mild
Weight per unit	3.1 (lbs/each)
Product Category	Conduit & Raceways

Features

outside diameter	4480
------------------	------

Dimensions and Weight

Length	25
--------	----

Descriptions

Description	4" UA SEALTITE CONDUIT, BONDED UL 25'
extra long description	SWC 55106704 LTM-UL 4" GYJT 25CN
Long Description	Titan2 Type UL LFMC is manufactured with a spiral wound strip of heavy gauge corrosion-resistant hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes the core is constructed with a square locked steel strip with an integral copperbonding strip enclosed within the steel convolutions. For 1-1/2" through 4" trade sizes the core is constructed with a fully interlocked steel strip. A rugged flame retardant flexible PVC jacket is extruded over the steel core. The grey jacket resists oils mild
Product Type	LTM-UI 4" Gyjt 25CN
Short Description	3 1/2" TITAN METAL-FLEX CONDUIT

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886053443
Manufacturers Part Number	55106704
UPC	032886053443

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441

Trade Size

Trade Size 4

Packaging

Carton 25

Weight Per each 3.1