



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UC133 2IN H-Duty GRND Conn

*Nsi Industries*

Catalog Number	UC133
Manufacturer	Nsi Industries
Description	The Nsi Uc-133 Bronze Heavy Duty U-Bolt Clamp Is Designed to Grip Rods and Ground 2" Ips Pipes In Parallel or 90-Degree Positions With An Easily Adjusted, Durably Strong Design. The High-Copper-Content Alloy Of The Clamp Provides Excellent Conductivity and Heavy-Duty Strength, Alongside The Silicon Bronze Nuts and Lockwashers. Use This U-Bolt For Demanding Applications In Harsh Environments, Including Direct Burial In Earth or Concrete. UI Listed 467 For Grounding and Bonding. Stock Products You Can Rely O
Weight per unit	1.1 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Clamp Material	250 MCM - 2/0 AWG
Insulation Material	Silicon Bronze



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2IN H-DUTY GRND CONN
extra long description	NSI UC-133 U Bolt Clamp 1 Cond. 2 P
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These heavy-duty bronze U-bolt clamps offer a durable and reliable solution for connecting a ground cable to a pipe, using the adjustable clamping structure. The gripping jaws feature a flexible design that fits a range of pipe sizes and can attach the grounding rod and pipe either in parallel or at a 90-degree angle. The bronze body has a high copper
Long Description	The NSI UC-133 Bronze Heavy Duty U-Bolt Clamp is designed to grip rods and ground 2" IPS pipes in parallel or 90-degree positions with an easily adjusted, durably strong design. The high-copper-content alloy of the clamp provides excellent conductivity and heavy-duty strength, alongside the silicon bronze nuts and lockwashers. Use this U-bolt for demanding applications in harsh environments, including direct burial in earth or concrete. UL Listed 467 for Grounding and Bonding. Stock products you can rely o
Product Type	U Bolt Clamp 1 Cond. 2 Pipe 250-2/0
Special Features	2 Pipe Size

## Manufacturer Information

Brand	NSi
GTIN	00662381108159
Manufacturers Part Number	UC-133
UPC	662381108159

## Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Ground Connector For Parrallel Copper Cables

## Packaging

Carton	1
Package	6
Weight Per each	1.09

## Uses, Certifications, and Standards

Application	Grounding Wire
standard	UL467