

Eaton UTH43369UCH

Catalog Number: UTH43369UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, #4-600 kcmil, 4-jaw, 1-ph, dual #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name	Catalog Number
Eaton meter socket	UTH43369UCH
UPC	Product Length/Depth
782113684086	5.69 in
Product Height	Product Width
36.63 in	15 in
Product Weight	Warranty
47 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

Line

#4-600 kcmil

Load

Dual #6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 320A 1P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTH43369UCH](#)

[Metering Equipment - Utilities Servicing Texas](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTH43369UCH

Catalog Number: UTH43369UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, #4-600 kcmil, 4-jaw, 1-ph, dual #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name	Catalog Number
Eaton meter socket	UTH43369UCH
UPC	Product Length/Depth
782113684086	5.69 in
Product Height	Product Width
36.63 in	15 in
Product Weight	Warranty
47 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

Line

#4-600 kcmil

Load

Dual #6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 320A 1P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTH43369UCH](#)

[Metering Equipment - Utilities Servicing Texas](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)