

# Eaton UTH7233UCH

Catalog Number: UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton meter socket	UTH7233UCH
UPC	Product Length/Depth
782116104208	5.63 in
Product Height	Product Width
27 in	16 in
Product Weight	Warranty
31 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Single-position commercial or residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

### Line

#6-350 kcmil

### Load

#6-350 kcmil

### Number of wires

Four-wire

### Hub type

5 x 5 hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

[Single Meter Sockets](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - SKT 200A 3P HCP](#)

### Specifications and datasheets

[Metering Equipment - Utilities Servicing Texas](#)

[Eaton Specification Sheet - UTH7233UCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UTH7233UCH

Catalog Number: UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



Photo is representative

## General specifications

Product Name

Eaton meter socket

UPC

782116104208

Product Height

27 in

Product Weight

31 lb

Catalog Number

UTH7233UCH

Product Length/Depth

5.63 in

Product Width

16 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Single-position commercial or residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

### Line

#6-350 kcmil

### Load

#6-350 kcmil

### Number of wires

Four-wire

### Hub type

5 x 5 hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

[Single Meter Sockets](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - SKT 200A 3P HCP](#)

### Specifications and datasheets

[Metering Equipment - Utilities Servicing Texas](#)

[Eaton Specification Sheet - UTH7233UCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)