



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UTH73369UHLCH 320A 3PH Oh/Ug 7TERM MTR SCKT W/ LVR Bypss *Eaton Corp*

Catalog Number	UTH73369UHLCH
Manufacturer	Eaton Corp
Description	
Weight per unit	40.0 (lbs/each)
Product Category	Commercial Single Meter Socket

Features

amperage rating	320 WTT
bypass	Lever bypass
dimensions	6.5000 IN X 20.0000 IN X 39.8900 IN
feed type	Top/bottom
Hub Type	5x5 hub cover plate
line	#14-1/0 AWG
Number of Jaws	Seven-jaws
Number of Sockets	1 PH
Number of Wires	Three-wire
Phase	1 PH
security	Ringless
Voltage Rating	600 WTT

Descriptions

Description	320A 3PH OH/UG 7TERM MTR SCKT W/ LVR BYPSS
Product Type	320A 3 PH MTR SKT Oh/Ug LG Hub CVR Plate

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116139323
Manufacturers Part Number	UTH73369UHLCH
sub brand	None Mount
UPC	782116139323

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
igcc	4314 CFM
Type	Single-position commercial or residential service
unspsc code	39121102

Packaging

Carton	1
Weight Per each	40



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	POWER DISTRIBUTION
standard	UL Listed



Powering Business Worldwide

pe.eaton.com

Eaton meter socket

UTH73369UHLCH

UPC:782116139323

Dimensions:

- **Height:** 39.89 IN
- **Length:** 6.5 IN
- **Width:** 20 IN

Weight:40 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-position commercial or residential service
- **Amperage Rating:** 320A
- **Feed Type:** Top/bottom
- **Hub Type:** 5x5 hub cover plate
- **Line:** #14-1/0 AWG
- **Number Of Jaws:** Seven-jaw
- **Phase:** Single-phase
- **Load:** #6-350 kcmil
- **Bypass:** Lever
- **Number Of Sockets:** 1
- **Number Of Wires:** Three-wire
- **Security:** Ringless
- **Voltage Rating:** 600V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - UTH73369UHLCH](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.