

Eaton UTTE7213TCH

Catalog Number: UTTE7213TCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, three-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton meter socket	UTTE7213TCH
UPC	Product Length/Depth
786685351346	4.94 in
Product Height	Product Width
19 in	13 in
Product Weight	Warranty
25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

IL : Ameren

MO : Ameren

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE7213TCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia

Eaton UTTE7213TCH

Catalog Number: UTTE7213TCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, three-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton meter socket	UTTE7213TCH
UPC	Product Length/Depth
786685351346	4.94 in
Product Height	Product Width
19 in	13 in
Product Weight	Warranty
25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

IL : Ameren

MO : Ameren

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE7213TCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)