



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VEM3546 1HP 1770RPM 3PH 60HZ 56C 3520M Tefc F1 N

Baldor/Abb Motors & Mechanical

Catalog Number	VEM3546
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Phase: 3 PH; Voltage Rating: 208-230/460 Vac; Torque Rating: 2.97 LB-FT Full Load, 12.5 LB-FT Break Down, 6.16 LB-FT Pull-Up, 8.49 LB-FT Locked-Roter At 460 V, 60 HZ, 1 HP; Insulation Class: F; Horsepower: 1 HP; Speed Rating: 17
Weight per unit	36.0 (lbs/each)
Product Category	Motors

Features

Base	No mounting
frame	56 V
horsepower	74565
Insulation Class	F
Phase	3 in
Power Factor	0.71 in
Service Factor	1.15 in
Speed Rating	1,760 rpm
Voltage Rating	208/230/460 V

Descriptions

Description	1HP 1770RPM 3PH 60HZ 56C 3520M TEFC F1 N
extra long description	BALDOR VEM3546 1HP,1760RPM,3PH,60HZ
Long Description	Baldor Electric; AC Motor; Phase: 3 PH; Voltage Rating: 208-230/460 VAC; Torque Rating: 2.97 LB-FT Full Load, 12.5 LB-FT Break Down, 6.16 LB-FT Pull-Up, 8.49 LB-FT Locked-Roter At 460 V, 60 HZ, 1 HP; Insulation Class: F; Horsepower: 1 HP; Speed Rating: 17
Product Type	1HP, 1760RPM, 3PH, 60HZ, 56C, 3519M, Tefc, F1, N
Special Features	1HP,1760RPM,3PH,60HZ,56C,3519M,TEFC,F1,N

Manufacturer Information

Brand	BALDOR
GTIN	00781568308608
Manufacturers Part Number	VEM3546
sub brand	Super-E
UPC	781568308608

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	36

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1