

**Eaton's Wiring Devices**  
Extra duty while-in-use protective cover

Extra duty, while-in-use  
**Weather  
Protective  
Covers**  
for code-compliant  
installations

**EATON**

*Powering Business Worldwide*




# Extra duty while-in-use weather protective cover



WIUX-1LPVGY



WIUX-1W



WIUX-1LPHCL



WIUX-2W



WIUX-1GY



WIUX-2CL

## Description

1-Gang & 2-Gang

## Design features

- Meets 2017 & 2020 406.9 (B)(1) Extra Duty requirement for any application
- Rugged UV-resistant polycarbonate cover and back protects devices without cracking or breaking and is non-corrosive
- No disassembly required for vertical or horizontal mounting orientation
- Vertical and horizontal mount wasp guards keep out unwanted pests
- 1-Gang box includes 3 inserts for 16 different configurations
- 2-Gang box includes 5 inserts for over 55 different configurations
- Box inserts accommodate decorator and GCFI devices, duplex receptacles, toggle switches and round receptacles
- Cover cord opening fits #12 AWG or lighter cord
- Exceeds UL outdoor low voltage landscape lighting requirements
- Box cover includes pre-mounted gasket

**Table 1. Extra duty while-in-use weather protective covers**

Catalog No.	Gang	Depth	Mounting Description	Material	Color
WIUX-1LPHGY	1	Low Profile	Horizontal	Polycarbonate	Gray
WIUX-1LPHCL	1	Low Profile	Horizontal	Polycarbonate	Clear
WIUX-1LPHW	1	Low Profile	Horizontal	Polycarbonate	White
WIUX-1LPVGY	1	Low Profile	Vertical	Polycarbonate	Gray
WIUX-1LPVCL	1	Low Profile	Vertical	Polycarbonate	Clear
WIUX-1LPVW	1	Low Profile	Vertical	Polycarbonate	White
WIUX-1GY	1	Standard	Vertical/Horizontal	Polycarbonate	Gray
WIUX-1CL	1	Standard	Vertical/Horizontal	Polycarbonate	Clear
WIUX-1W	1	Standard	Vertical/Horizontal	Polycarbonate	White
WIUXM-1GY	1	Standard	Vertical/Horizontal	Die cast aluminum	Gray
WIUXM-1W	1	Standard	Vertical/Horizontal	Die cast aluminum	White
WIUX-2GY	2	Standard	Vertical	Polycarbonate	Gray
WIUX-2CL	2	Standard	Vertical	Polycarbonate	Clear
WIUX-2W	2	Standard	Vertical	Polycarbonate	White
WIUXM-2GY	2	Standard	Vertical	Die cast aluminum	Gray
WIUXM-2W	2	Standard	Vertical	Die cast aluminum	White

cCSAus Certified to UL514D, file no. 174008, meets NEMA 3R requirements

**Compliances, specifications and availability are subject to change without notice.**

Electrical Sector  
1123 HWY 74 S  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/wiringdevices

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/wiringdevices

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 178 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, México CP 54800  
México  
Eaton.mx  
Eaton.com/wiringdevices