

Weather Proof Cover - Extra-Duty Die-Cast In-Use Weatherproof Cover, Single-Gang, Vrt, 3.125" Gray

Item WP1010MXD



c 🖳 us 🥵

PRODUCT DESCRIPTION

Die-Cast In-Use Aluminum Weatherproof Covers are extra-duty rated and easy to install. Heavy-duty die-cast aluminum construction ensures long-lasting durability. Covers come with a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ► Complies with 2020 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications
- ► CEC Article 26-702 Compliant
- ► UL Certified for Type 3R outdoor enclosures
- ► Meets requirements for cold impact testing: -60° F (-51° C)
- > Heavy-duty die-cast aluminum cover and mounting base with UV stabilized polycarbonate inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- Lockable hasp: All models accept up to 1/4" (6 mm) dia shank
- Impact rated: 12 lbf. impact test to ensure cover remains intact
- Reinforced hinge pin designed to exceed 40 lbf. hinge hang/stress test
- ► Warranty: 1-year limited
- Three inserts provided with all models that allow each model to meet multiple installations (up to 8 configurations)
- ► Max cord size: #12 AWG or smaller

APPLICATIONS

- Engine Block Heaters
- ► Receptacle Protection
- ► Walk-in Refrigeration Cooler/Freezer

TECHNICAL DATA

General	
Model Number	WP1010MXD
Description	Extra-Duty Die-Cast In-Use Weatherproof Cover, Single-Gang, Vrt, 3.125" Gray
UPC Code	078275130135
Brand	Intermatic
Country of Origin (Intermatic)	CHINA
Warranty Period	1-Year limited
Mechanical Specifications	
Number of Included Inserts	3
Insert Types Included	WP17
Hinge Direction	Vertical
Is Extra-Duty Rated	Yes
Dimensions	
Product Dimensions (H x W x D) in	6 3/8 x 3 4/5 x 3 1/8 in
Accepted Cord Size Max	1x12 AWG
Вох Туре	Single
Material Specifications	
Color	Gray



Weatherproof Cover Material	Die-Cast Aluminum
Packaging	
Shipping Weight (Ibs)	1.27
Unit Carton Dimensions (H x W x L) in	3.25 x 3.875 x 6.375 in
Standards and Certifications	
UL Certification	cULus
CSA Certification	cCSAus
Other Certifications and Compatibilities	REACH
California Proposition 65	None



ACCESSORIES



WP17 Single-Gang Inserts (3)