



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WPRB11 4" RND WP Gray Lamp Cover - One 1/2" Hole

*Pass & Seymour/Legrand*

Catalog Number	WPRB11
Manufacturer	Pass & Seymour/Legrand
Description	Weatherproof Cluster Cover, Die-Cast Aluminum, Gray, Rectangular, 4 In Diameter, Wall Mount, 0.34 LB/Ea
Weight per unit	0.3425 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

### Features

number of outlet	1 PH
------------------	------

### Dimensions and Weight

Size	6" IN
------	-------

### Descriptions

Construction	Weatherproof
Description	4" RND WP GRAY LAMP COVER - ONE 1/2" HOLE
Special Features	Heavy duty die cast zinc, cord flap gasket

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007117066
UPC	785007117066

### Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	Weatherproof Cover

### Packaging

Carton	1
Package	8
Weight Per each	0.3425

### Uses, Certifications, and Standards

Mounting	WALL
standard	UL Listed

---

## 4" ROUND OUTDOOR CLUSTER COVER, GRAY

WPRB11 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Weatherproof 4" Round Outdoor Cluster Cover, Blank 1 Hole 1/2" With Gasket and Screws, Gray



- Wide range of rectangular and round covers.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- Kits available combining fixtures, lamp covers, and accessories.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Size: 4"  
Type: Lighting Cluster Covers  
Style: 4" Round Outdoor

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121305  
UR: No

#### DIMENSIONS

Diameter (US): 4"

## TECHNICAL INFORMATION

Shape: Round

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: INDIA

Buy American Act Status: No