



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 Commerce Rd
71601-7613, AR Pine Bluff
Phone: 870-671-4805
Fax: 870-671-4806



WPG1 Weather Proof Cover Flanged Inlets/Outlets 1.96

Pass & Seymour/Legrand

Catalog Number	WPG1
Manufacturer	Pass & Seymour/Legrand
Description	Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet, 1.96-Inch Diameter Opening to Accommodate 15/20A Straight Blade, 15A Turnlok Registered, 20403 Power Interrupter
Weight per unit	0.3030 (lbs/each)
Product Category	Wall Plates & Covers

Features

Cover Type	Weatherproof
indoor/outdoor	Outdoor
insulation	Box
Material	Thermoplastic
Mounting Type	Box Mounted
Number of Gangs	1
number of outlet	1
Number of Outlets	1.0
Wall Plate Type	Custom

Material, Color, and Finish

Color	Gray
Finish	Matte

Dimensions and Weight

Size	6"
------	----

Descriptions

Construction	Weatherproof
Description	WEATHER PROOF COVER FLANGED INLETS/OUTLETS 1.96
extra long description	P&S WPG1 WP CVR FLANGED INLETS/OUTL
Features	Weatherproof
Long Description	Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet, 1.96-inch Diameter Opening to Accommodate 15/20A Straight Blade, 15A Turnlok Registered, 20403 Power Interrupter
Product Type	WP CVR Flanged Inlets/Outlets 1.96
Special Features	Heavy duty die cast zinc, cord flap gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 Commerce Rd
71601-7613, AR Pine Bluff
Phone: 870-671-4805
Fax: 870-671-4806

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007065305
Manufacturers Part Number	WPG-1
UPC	785007065305

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	Weatherproof Cover

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.303

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL cULus, UL Listed