ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# WT11 Wiretwist Wire Connector, WT1 Gray, 100/Box

*Ideal*

| | |
|---|---|
| Catalog Number | WT11 |
| Manufacturer | Ideal |
| Description | Wire Twist Connector, (3) #22 Awg Conductor Size, (2) #16 Awg Conductor Size, Gray Insulation Color, +221 °F Operating Temperature, 1 to 5 Conductors, 300 V, 0.15 LB |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Electrical Fixture Conn ( Nuts |

## Features

| | |
|---|---|
| Material | Flame-retardant Polypropelene |
| Voltage Rating | 300 |

## Material, Color, and Finish

| | |
|---|---|
| Color | Gray |

## Descriptions

| | |
|---|---|
| Description | WIRETWIST WIRE CONNECTOR, WT1 GRAY, 100/BOX |
| extra long description | IDEAL WT1-1 WIRE-TWIST CONN.,GREY,B |
| Features | With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance.The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing |

## Manufacturer Information

| | |
|---|---|
| Brand | Buchanan |
| GTIN | 00781789610009 |
| UPC | 781789610009 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | WIRE NUTS |

## Availability

| | |
|---|---|
| minimum qty | 100 |

## Packaging

| | |
|---|---|
| Carton | 100 |
| Package | 1000 |
| Weight Per each | 0.15 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Insulating or Joining 1 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA C22.2 #188, UL 486C Listed, RoHS |