



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WR8212 #8 X 2-1/2" Phil BH Coarse Thread Drywall Screw

L.H. Dottie CO.

Catalog Number	WR8212
Manufacturer	L.H. Dottie CO.
Description	Bugle Head Wood Rocket Drywall Screw, Steel Material, #8 X 2-1/2 In. Size, 2-1/2 In. Length, Coarse Thread Type, #8 Thread Size, Yellow Head Color, Yellow Zinc Finish, Phillips Drive, Drywall Screw Type, Self Piercing, Patented Invincibox Packaging
Weight per unit	0.0110 (lbs/each)
Product Category	Screws, Nuts, Bolts, Washers

Features

Head Type	Bugle
Material	Steel
Point Type	Self Piercing
Screw Type	Drywall
Thread Size	#8
Thread Type	Coarse

Material, Color, and Finish

Finish	Yellow Zinc
--------	-------------

Dimensions and Weight

Length	2-1/2
Size	#8 x 2-1/2 IN

Descriptions

Description	#8 X 2-1/2" PHIL BH COARSE THREAD DRYWALL SCREW
extra long description	DOTTIE WR8212 8 X 2-1/2 Drywall Scr
Long Description	Bugle Head Wood Rocket Drywall Screw, Steel material, #8 x 2-1/2 in. Size, 2-1/2 in. length, Coarse thread type, #8 thread size, Yellow head color, Yellow Zinc finish, Phillips drive, Drywall screw type, Self Piercing, Patented Invincibox Packaging
Product Type	8 X 2-1/2 Drywall Screws Phillips Bugle Head Coarse
Special Features	Features: Wood Rocket, Invincibox Up to 2 Inch

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002162094
Manufacturers Part Number	WR8212
UPC	781002162094

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Bugle Head Wood Rocket Drywall Screw



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Weight Per each	0.011

Uses, Certifications, and Standards

Application	Drywall, Particle Board, Wood
-------------	-------------------------------