



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918



WT6B Wiretwist Wire Connector, WT6 Red, 250/Bag

Ideal

| | |
|------------------|---|
| Catalog Number | WT6B |
| Manufacturer | Ideal |
| Description | Buchanan, Wire Connector, Wiretwist, Conductor Range: 18 - 8 Awg, 2/14 Awg Min, 4/12 Awg Max, Number Of Conductors: 1 to 5, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT6 |
| Weight per unit | 0.0060 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|-------------------------------|
| Material | Flame-retardant Polypropelene |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Red |
|-------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918

Descriptions

| | |
|------------------------|--|
| Description | WIRETWIST WIRE CONNECTOR, WT6 RED, 250/BAG |
| extra long description | IDEAL WT6-B WIRE-TWIST CONN.,RED,BA |
| Features | With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing |
| Long Description | Buchanan, Wire Connector, WireTwist, Conductor Range: 18 - 8 AWG, 2/14 AWG Min, 4/12 AWG MAX, Number Of Conductors: 1 to 5, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT6 |
| Product Type | Wire-Twist Conn., Red, Bag 250 |
| Special Features | 1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT6;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL 486C Listed And CSA 22.2 #188 Certified |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Buchanan |
| GTIN | 00781789610092 |
| Manufacturers Part Number | WT6-B |
| UPC | 781789610092 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
|----------------------|-----------|

Availability

| | |
|-------------|-----|
| minimum qty | 250 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 5000 |
| Weight Per each | 0.006 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2818 NE Independence Avenue
64064-0000, MO Lee's Summit
Phone: 816-924-7000
Fax: 816-931-2918

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Insulating or Joining 1 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA C22.2 #188, UL 486C Listed, RoHS |